F090BBS2



FlexTwist® Flexible Twist for WR90, 8.2–12.4 GHz, with interface types UG-39/U and UG-39/U, 600 mm

Product Classification

Product Type Rectangular waveguide, flexible twist

Product Brand FlexTwist®

General Specifications

Component Flexible Twist

 Interface
 UG-39/U

 Interface 2
 UG-39/U

Dimensions

 Length
 600 mm | 23.622 in

 Waveguide Size
 WR90 | WG16 | R100

Electrical Specifications

Attenuation 0.43 dB/m | 0.131 dB/ft

Average Power 960 W

Operating Frequency Band 8.2 – 12.4 GHz

 Peak Power
 180 kW

 VSWR
 1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)64 mm | 2.52 inMinimum Bend Radius, Multiple Bends (H Plane)127 mm | 5 in

 Maximum Twist
 310 °/m | 94.488 °/ft

 Pressurization, maximum
 0.31 N/mm² | 45 psi



F090BBS2

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

