

# F090KMB2



FlexTwist® Flexible Twist for WR90, 10.7–11.7 GHz, with interface types PBR100 and UBR100, 600 mm

## Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

## General Specifications

Component	Flexible Twist
Interface	PBR100
Interface 2	UBR100

## Dimensions

Length	600 mm   23.622 in
Waveguide Size	WR90   WG16   R100

## Electrical Specifications

Attenuation	0.43 dB/m   0.131 dB/ft
Average Power	960 W
Operating Frequency Band	10.7 – 11.7 GHz
Peak Power	180 kW
VSWR	1.05

## Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	64 mm   2.52 in
Minimum Bend Radius, Multiple Bends (H Plane)	127 mm   5 in
Maximum Twist	310 °/m   94.488 °/ft
Pressurization, maximum	0.31 N/mm²   45 psi

# F090KMB2

---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

