F090LLB2



FlexTwist® Flexible Twist for WR90, 10.7–11.7 GHz, with interface types UDR100 and UDR100, 600 mm

Product Classification

Product Type Rectangular waveguide, flexible twist

Product Brand FlexTwist®

General Specifications

Component Flexible Twist

InterfaceUDR100Interface 2UDR100

Dimensions

 Length
 600 mm | 23.622 in

 Waveguide Size
 WR90 | WG16 | R100

Electrical Specifications

Attenuation 0.43 dB/m | 0.131 dB/ft

Average Power 960 W

Operating Frequency Band 10.7 – 11.7 GHz

 Peak Power
 180 kW

 VSWR
 1.05

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)64 mm | 2.52 inMinimum Bend Radius, Multiple Bends (H Plane)127 mm | 5 in

 Maximum Twist
 310 °/m | 94.488 °/ft

 Pressurization, maximum
 0.31 N/mm² | 45 psi



F090LLB2

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

