

F090LMS3



FlexTwist® Flexible Twist for WR90, 8.2–12.4 GHz, with interface types UDR100 and UBR100, 900 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	UDR100
Interface 2	UBR100

Dimensions

Length	900 mm 35.433 in
Waveguide Size	WR90 WG16 R100

Electrical Specifications

Attenuation	0.43 dB/m 0.131 dB/ft
Average Power	960 W
Operating Frequency Band	8.2 – 12.4 GHz
Peak Power	180 kW
VSWR	1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	64 mm 2.52 in
Minimum Bend Radius, Multiple Bends (H Plane)	127 mm 5 in
Maximum Twist	310 °/m 94.488 °/ft
Pressurization, maximum	0.31 N/mm ² 45 psi

Regulatory Compliance/Certifications

F090LMS3

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

