

# 8-1553415-4

Fiber Optic Cable, dualan, OFNP, OM3, 2.9 mm, violet

## Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-DS

## General Specifications

Cable Type	Tight buffer
Jacket Color	Violet
Jacket Marking	Meters
Fibers per Subunit, quantity	2
Total Fiber Count	2

## Dimensions

Cable Length	1000 m   3,280.84 ft
Diameter Over Jacket	2.9 mm   0.114 in

## Optical Specifications

Fiber Type	OM3
------------	-----

## Optical Specifications, Wavelength Specific

Bandwidth, Laser, minimum	2,000 MHz-km @ 850 nm
Standards Compliance	TIA-492AAAC (OM3)

## Environmental Specifications

Environmental Space	Plenum
---------------------	--------

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

8-1553415-4

---

ROHS	Compliant
UK-ROHS	Compliant

