

F112HLC5



FlexTwist® Flexible Twist for WR112, 7.125–8.5 GHz, with interface types PDR84 and UDR84, 1200 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PDR84
Interface 2	UDR84

Dimensions

Length	1200 mm 47.244 in
Waveguide Size	WR112 WG15 R84

Electrical Specifications

Attenuation	0.4 dB/m 0.122 dB/ft
Average Power	1260 W
Operating Frequency Band	7.125 – 8.5 GHz
Peak Power	315 kW
VSWR	1.05

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	76 mm 2.992 in
Minimum Bend Radius, Multiple Bends (H Plane)	152 mm 5.984 in
Maximum Twist	264 °/m 80.467 °/ft
Pressurization, maximum	0.241 N/mm ² 35 psi

F112HLC5

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

