## F112HMS3



FlexTwist® Flexible Twist for WR112, 7.05–10.0 GHz, with interface types PDR84 and UBR84, 900 mm

### **Product Classification**

Product Type Rectangular waveguide, flexible twist

Product Brand FlexTwist®

General Specifications

**Component** Flexible Twist

InterfacePDR84Interface 2UBR84

**Dimensions** 

 Length
 900 mm | 35.433 in

 Waveguide Size
 WR112 | WG15 | R84

**Electrical Specifications** 

**Attenuation** 0.4 dB/m | 0.122 dB/ft

Average Power 1260 W

**Operating Frequency Band** 7.05 – 10.0 GHz

 Peak Power
 315 kW

 VSWR
 1.1

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)76 mm | 2.992 inMinimum Bend Radius, Multiple Bends (H Plane)152 mm | 5.984 inMaximum Twist264 °/m | 80.467 °/ftPressurization, maximum0.241 N/mm² | 35 psi



# F112HMS3

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

