2-599156-4 | C-012-CN-8W-M12YL/28D/AY/D



Fiber Indoor/Outdoor Cable, 12-fiber, singlemode G.652.D and G.657.A1, Gel-free, yellow jacket color, Dca Flame Rating, Meters jacket marking, 2000 meters

Product Classification


Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-CN
General Specifications	
Cable Type	Loose tube
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Meters
Fibers per Subunit, quantity	12
Total Fiber Count	12
Dimensions	
Cable Length	2000 m 6,561.68 ft
Diameter Over Jacket	6.4 mm 0.252 in

Representative Image

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025





Mechanical Specifications

Minimum Bend Radius, loaded	139.7 mm 5.5 in
Minimum Bend Radius, unloaded	129.5 mm 5.098 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	500 N 112.404 lbf

Optical Specifications

Fiber Type

G.652.D and G.657.A1

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.25 dB/km @ 1,300 nm 0.35 dB/km @ 1,550 nm 0.45 dB/km @ 1,310 nm
Standards Compliance	IEC 60794-1 TIA-492CAAB (OS2)

Environmental Specifications

Installation temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



2-599156-4 | C-012-CN-8W-M12YL/28D/AY/D

EN50575 CPR Cable EuroClass Droplets Rating	d2
EN50575 CPR Cable EuroClass Acidity Rating	al
Environmental Space	Universal Low Smoke Zero Halogen (ULSZH)
Packaging and Mojepts	

Packaging and Weights

Cable weight

31 kg/km | 20.831 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 8W-250um

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

