

3-1553415-8

Fiber Optic Cable, dualan, 2-fiber, OFNP, 2.9 mm, OM3, white

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-DS

General Specifications

Cable Type	Tight buffer
Jacket Color	White
Jacket Marking	Meters
Fibers per Subunit, quantity	2
Total Fiber Count	2

Dimensions

Cable Length	1000 m 3,280.84 ft
Diameter Over Jacket	2.9 mm 0.114 in

Optical Specifications

Fiber Type	OM3
------------	-----

Optical Specifications, Wavelength Specific

Bandwidth, Laser, minimum	2,000 MHz-km @ 850 nm
Standards Compliance	TIA-492AAAC (OM3)

Environmental Specifications

Environmental Space	Plenum
---------------------	--------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

3-1553415-8

ROHS	Compliant
UK-ROHS	Compliant

