4-1553419-9

Fiber Optic Cable, quad, 4-fiber, OFNP, OM4, 4.8 mm, aqua

Product Classification

Regional Availability

Asia | Latin America | North America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-DS

General Specifications

Cable TypeTight buffer

Jacket ColorAquaJacket MarkingMeters

Fibers per Subunit, quantity 4

Total Fiber Count 4

Dimensions

Diameter Over Jacket 4.8 mm | 0.189 in

Mechanical Specifications

Minimum Bend Radius, loaded96 mm3.78 inMinimum Bend Radius, unloaded48 mm1.89 inTensile Load, long term, maximum31 N | 6.969 lbfTensile Load, short term, maximum98 N | 22.031 lbf

Optical Specifications

Fiber Type OM4, LazrSPEED®

Optical Specifications, Wavelength Specific

10 Gbps Ethernet Distance 550 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.20 dB/km @ 850 nm

Bandwidth, Laser, minimum 4,700 MHz-km @ 850 nm

Bandwidth, OFL, minimum 3,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

Standards Compliance ANSI/TIA-568.B.1 | ANSI/TIA-568.B.2 | IEC 60793-2-10 | TIA-492AAAD (OM4)

COMMSCOPE®

4-1553419-9

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature $0 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Environmental Space Plenum

Packaging and Weights

Cable weight 30 kg/km | 20.159 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

