

RapidFiber® EFDT NID Wall Mounting Fiber Box, outdoor, 12 SC/APC, 4-way splitter

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber wall box
Product Brand	RapidFiber®
Product Series	EFDT


General Specifications

Functionality	Patching Splitting
Access	Front
Distribution Type	1 x 4 splitter
Enclosure Color	Gray
Front Cover Type	Hinged with lock
Interface	SC/APC
Mounting	Wall
Port, quantity	12
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	264.16 mm 10.4 in
Width	179.07 mm 7.05 in
Depth	71.12 mm 2.8 in

Ordering Tree



Material Specifications

Enclosure Material Type LSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1

Insertion Loss, Splitter, maximum 7.7 dB

Return Loss, Connector, minimum 55 dB

Environmental Specifications

Environmental Space Outdoor

Qualification Standards IEC 60529, IP55 | IEC 61753-1, category G

Packaging and Weights

Packaging quantity 8

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

