

A-100454

Base Product



Single Phase Meter Pillar Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Power supply enclosure

General Specifications

Access	Front door
Accessories	Cable plate In-ground root
Batteries Supported	0
Batteries Supported, with optional battery pedestal	0
Cabinet Type	Meter cabinet
Color	Gray Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Door Security	7 mm triangle lock
Internal Mounting Surface	12 mm plywood backboard

Dimensions

Height	863.6 mm 34 in
Width	381 mm 15 in
Depth	177.8 mm 7 in
Depth, without door	177.8 mm 7 in

Electrical Specifications

ac Distribution Type	6-way metal enclosure
ac Feeds, Outgoing, quantity	4
Generator Connection	No connection
Power Phase	Single
Voltage	230 Vac

Material Specifications

A-100454

Finish	Powder coated
Material Type	Galvanized steel

Packaging and Weights

Weight, net	19.958 kg 44 lb
--------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system