

A-100458

Combiner/ Mast head amplifier enclosure for micro cell sites

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Micro cell site enclosure

Ordering Note For UK region only

General Specifications

Access Front door

Batteries Supported 0

Cabinet Type Combiner cabinet

Color Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

Door Security Swing handle with 22mm profile cylinder

Doors, quantity 2

Mounting Plinth | Root

Dimensions

Height 1,346.2 mm | 53 in

Width 1,574.8 mm | 62 in

Depth 381 mm | 15 in

Electrical Specifications

Generator Connection No connection

Rectifiers, quantity 0

Material Specifications

Finish Powder coated

Material Type Galvanized steel

Environmental Specifications

Qualification Standards IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP45

A-100458

Packaging and Weights

Included Brackets | Installation Kit

Weight, net 97.976 kg | 216 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

