

# A-100880

## Base Product



## Meter Cabinet with Backboard Only

- Sealed to outside environment
- Double wall construction

## Product Classification

**Product Type** Power supply enclosure

## General Specifications

**Access** Front door

**Accessories** Cable plate | In-ground root | Plinth

**Batteries Supported** 0

**Batteries Supported, with optional battery pedestal** 0

**Cabinet Type** Meter cabinet

**Color** Green | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

**Door Security** 7 mm triangle lock

**Internal Mounting Surface** 12 mm plywood backboard

## Dimensions

**Height** 1016 mm | 40 in

**Width** 660.4 mm | 26 in

**Depth** 254 mm | 10 in

**Depth, without door** 254 mm | 10 in

## Electrical Specifications

**ac Feeds, Outgoing, quantity** 0

**Generator Connection** No connection

## Material Specifications

**Finish** Powder coated

**Material Type** Galvanized steel

# A-100880

---

## Packaging and Weights

**Weight, net**

35.834 kg | 79 lb

## Regulatory Compliance/Certifications

**Agency**

**Classification**

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system