CS6975-000 | BUDI-M-TB-B



BUDI™ Fiber Optic Wall mount Enclosure, empty for holding PON Application kits, with lock

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

Product Classification

Regional Availability EMEA

Portfolio CommScope®
Product Type Fiber wall box

Product Brand BUDI™
Product Series BUDI-M

General Specifications

Functionality Patching | Splicing

Access Front
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceUnloadedLock TypeKey lockMountingWall

Dimensions

 Height
 480 mm | 18.898 in

 Height, with cover
 550 mm | 21.654 in


 Width
 360 mm | 14.173 in

 Depth
 175 mm | 6.89 in

Dimension Drawing



CS6975-000 | BUDI-M-TB-B



Material Specifications

Enclosure Material Type LSZH thermoplastic

Environmental Specifications

Environmental Space Indoor/Outdoor

Qualification Standards IEC 60529, IP54 | IEC 61753-1, category G

Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

