# CW7713-000 | BUDI-S-T-B-24L100NN



# BUDI™ Fiber Optic Wall mount Enclosure, 24 LC/UPC ports, with FIST Management System

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

#### **Product Classification**

Regional Availability EMEA

PortfolioCommScope®Product TypeFiber wall box

Product Brand BUDI™
Product Series BUDI-S

#### General Specifications

Functionality Patching | Splicing

Access Front
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceLC/UPCMountingWallPort, quantity24

#### **Dimensions**

 Height
 425 mm | 16.732 in

 Height, with cover
 500 mm | 19.685 in


 Width
 155 mm | 6.102 in

 Depth
 60 mm | 2.362 in

#### Dimension Drawing



# CW7713-000 | BUDI-S-T-B-24L100NN



## Material Specifications

**Enclosure Material Type** LSZH thermoplastic

### **Optical Specifications**

**Fiber Mode** Singlemode

#### **Environmental Specifications**

**Environmental Space** Indoor/Outdoor

**Qualification Standards** IEC 60529, IP54 | IEC 61753-1, category G

## Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

#### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



**COMMSCOPE®**