CX1963-000 | IWB24-SC-FS-12-00-21

IWB Fiber Wall Box, 2-door, singlemode SC/UPC, 12-ports, partially loaded, no pigtails and splice tray, 2 cable clamps

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional Availability	Asia | EMEA
Product Type	Fiber wall box
Product Series	IWB

General Specifications

Application	Patching | Splicing
Adapters, quantity	12
Cable Clamps, quantity	2
Cable Entry Location	Bottom right | Top right
Color	Gray
Door, quantity	2
Front Door Type	Single hinged
Interface, front	SC
Interface Feature, front	Standard
Mounting	Wall
Splice Trays Included, quantity	1
Splicing Capacity, maximum	12
Splicing Type	Mass fusion
Total Ports, quantity	12

Dimensions

Height	350 mm | 13.78 in
Width	425 mm | 16.732 in

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 22, 2020

Depth	85 mm | 3.346 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA type 12

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag | Carton

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 22, 2020