## CZ5633-000 | FIST-GPSTF-12-AFN-2



FIST GPST Fiber Patch/Splice Tray, 12/24 ports, no adapters, ANT splice chip, 15 in, gray, right patch cord routing

#### **Product Classification**

Regional Availability EMEA

Product Type Fiber patch/splice tray

Product Brand FIST®

Product Series FIST-GPST

## General Specifications

Functionality Patching | Splicing

**Color** Gray

Interface, front Unloaded

Patch Cord Entry Location Front, right side

**Splicing Type** ANT, single fiber fusion

Total Ports, quantity 12

#### Dimensions

 Height
 16 mm | 0.63 in

 Width
 315 mm | 12.402 in

 Depth
 190 mm | 7.48 in

### **Optical Specifications**

**Fiber Mode** Singlemode

## **Environmental Specifications**

Operating Temperature  $-5 \degree \text{C to } +45 \degree \text{C (} +23 \degree \text{F to } +113 \degree \text{F)}$ Storage Temperature  $-30 \degree \text{C to } +60 \degree \text{C (} -22 \degree \text{F to } +140 \degree \text{F)}$ 

Page 1 of 2



# CZ5633-000 | FIST-GPSTF-12-AFN-2

**Relative Humidity** Up to 93%, non-condensing

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

