EM1622-001 | SCIL-B-24A-1-S2-NN



SCIL-B Fiber splice closure, in-line, with 2 gel cable sealing kits, 1 pre-installed 24A-splice tray and SMOUV protectors, no ground feedtrough lug, no air valve

- Leverages proven FOSC™ fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Product Type In-line, rectangular fiber closure

Product Brand SCIL™
Product Series SCIL-B

General Specifications

 Cable Entry Drop Port Style
 Round

 Cable Entry Main Port Style
 Round

Cable Ports Quantity, total 4 multi-out ports (24 cables)

Cable Sealing Type Compressed gel

Closure Sealing Type Side latch

Closure StyleIn-lineColorBlackFlash Test ValveNoneGround Feed-throughNone

Mounting Pole | Strand | Wall

Network Area Type Drop

Splice Tray Included, quantity

Splice Tray Type Included 24-way, heat shrink

Splicing Capacity, Single Fusion, maximum 96
Splicing Capacity, Single Splice, 12 fibers, maximum 96

Splicing Type, Supported Single fusion

COMMSCOPE®

EM1622-001 | SCIL-B-24A-1-S2-NN

Dimensions


 Height
 106 mm | 4.173 in


 Width
 182 mm | 7.165 in

Length 369 mm | 14.528 in

Main Cable Diameter, maximum 22 mm | 0.866 in

Ordering Tree





Material Specifications

Material Type Rugged polymer

Environmental Specifications

Environmental SpaceAbove ground| Below groundQualification StandardsIEC 60529, IP68 + 2 m waterhead

Packaging and Weights

Included SMOUV splice protectors (24)

Packaging quantity

Page 2 of 3

EM1622-001 | SCIL-B-24A-1-S2-NN

Packaging TypeBox| CartonWeight, net1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant

