# EM1624-001 | SCIL-B-24-1-S2-NN



SCIL-B Fiber splice closure, in-line, with 2 gel cable sealing kits, 1 pre-installed 24-splice tray and SMOUV protectors, no ground feedtrough lug, no air valve

- Leverages proven FOSC™ fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Product Type In-line, rectangular fiber closure

Product Brand SCIL™
Product Series SCIL-B

General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleRound

**Cable Ports Quantity, total** 4 multi-out ports (24 cables)

Cable Sealing Type Compressed gel

Closure Sealing Type Side latch

Closure StyleIn-lineColorBlackFlash Test ValveNoneGround Feed-throughNone

Mounting Pole | Strand | Wall

Network Area Type Drop

Splice Tray Included, quantity

**Splice Tray Type Included** 24-way, heat shrink

Splicing Capacity, Single Fusion, maximum 96
Splicing Capacity, Single Splice, 12 fibers, maximum 96

**Splicing Type, Supported** Single fusion

Page 1 of 3



## EM1624-001 | SCIL-B-24-1-S2-NN

#### **Dimensions**


**Height** 106 mm | 4.173 in


**Width** 182 mm | 7.165 in

**Length** 369 mm | 14.528 in

Main Cable Diameter, maximum 22 mm | 0.866 in

#### Ordering Tree





#### Material Specifications

Material Type Rugged polymer

## **Environmental Specifications**

Environmental SpaceAbove ground| Below groundQualification StandardsIEC 60529, IP68 + 2 m waterhead

Packaging and Weights

Included SMOUV splice protectors (24)

Packaging quantity

Page 2 of 3

# EM1624-001 | SCIL-B-24-1-S2-NN

Packaging TypeBox| CartonWeight, net1 kg | 2.205 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant

