FPS-LPP1JJJ



FDH 3000 Plug-and-Play Splitter Module, 1×8 , SC/APC, Build America Buy America (BABA)

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability Latin America | North America

PortfolioCommScope®Product TypeSplitter module

Product Series FDH 3000 | Mini FDH 3000

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Interface, rear

Device Type Plug-and-play module

Functionality Splitting

Access Front | Rear

Application For use in FDH 3000 cabinets

Circuits, quantity 1

 Distribution Type
 1 x 8 splitter

 Interface, front
 SC/APC

 Interface, Input
 SC/APC

 Interface, Output
 SC/APC

Location of Manufacturing Waived per BABA waiver for BEAD Program

Module ColorPutty whiteSplit RatioSymmetrical

Page 1 of 2



SC/APC

FPS-LPP1JJJ

Splitter, quantity 1

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 12.7 mm | 0.5 in

 Depth
 139.7 mm | 5.5 in

 Furcation Tube Diameter
 2 mm | 0.079 in

Optical Specifications

Directivity, minimum55 dBPolarization Dependent Loss, maximum0.2 dBUniformity, maximum1 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum10.4 dBReturn Loss, Splitter, minimum55 dB

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Flammability Rating UL 94 V-0

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE | Telcordia GR-326-CORE

Packaging and Weights

Included Reversible dust cap

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



