

FPS-MPP4AJJ



Singlemode Splitter Module, 1 x 32, SC/APC, symmetrical split ratio, 126" Pigtail

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

OBSOLETE
This product was discontinued on: December 30, 2018

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter module
Product Series	FDH 3000
Government Requirements	Build America Buy America (BABA) compliant*

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Access	Front
Application	For use with OMX frames
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Interface, rear	SC/APC
Location of Manufacturing	Waived per BABA waiver for BEAD Program
Module Color	Putty white
Split Ratio	Symmetrical

FPS-MPP4AJJ

Splitter, quantity 1

Optical Specifications

Directivity, minimum 60 dB

Insertion Loss, Splitter, maximum 16.7 dB

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

