

FPX-12MPLSOJ



FPX Fiber Optic MPO Module, Singlemode OS2, 12 fiber SC/APC adapter, left, putty white

- FPX modules offer the end-user the flexibility of a plug-and-play MPO architecture with a “grow as you go” approach to the network
- Each module has a front bulkhead identical to the adapter pack with an internal cable assembly converting to an MPO male connector
- All fiber connectivity is housed in an enclosed module with a rear MPO adapter allowing the user to utilize an MPO trunk to turn up service

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	FPX

General Specifications

Functionality	Breakout
Application	For use with FPX panels
Adapter Color	Green
Adapters, quantity, front	12
Adapters, quantity, rear	1
Body Style	Left orientation Simplex
Color, front	Putty white
Color, housing	Putty white
Color, rear	Putty white
Interface, front	SC/APC
Interface, rear	MPO
Interface Feature, rear	APC
Polarity	Pairs, straight
Total Ports, quantity, front	12


Dimensions

Height	33.02 mm 1.3 in
--------	-------------------

FPX-12MPLSOJ

Width	176.53 mm 6.95 in
Depth	127 mm 5 in

Ordering Tree



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.25 dB
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

FPX-12MPLSOJ

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant

