

FSB-SGJ27200C00000



FSB Fiber Splitter Box, outdoor, SC/APC, 72 ports, heat shrink splice tray, 3 splitter slots, putty white

Product Classification

Regional Availability	North America
Product Type	Fiber wall box
Product Series	FSB

General Specifications

Functionality	Patching Splicing Splitting
Access	Front
Cable Color	White
Cable Type	Pigtails - Stranded
Enclosure Color	Putty white
Interface	SC/APC
Lock Type	Padlock ready
Mounting	Wall
Port Capacity, maximum	72
Port, quantity	72

Dimensions

Height	330.2 mm 13 in
Width	482.6 mm 19 in
Depth	254 mm 10 in

Ordering Tree

FSB-SGJ27200C00000

FSB-

Configuration

S

Standard

Enclosure Type

Code	Description	Capacity	Size (HxWxD)
B	Indoor FSB-32	32-Fiber	8"x13.5"x5"
G	Outdoor FSB-72	72-Fiber	13.5"x19"x8"
H	Indr/Outdr FSB-16	16-Fiber	9"x9"x3.7"

Connector Type

J

SC/APC

N

SC/UPC

Splice Tray (Feeder Side)

2

Heat Shrink Fusion

3

Mechanical/Ribbon

0

No Splice Tray

Fiber Count (Distribution)

12

12 Fibers

16

16 Fibers

32

32 Fibers

48

48 Fibers

72

72 Fibers

Splitter Type Installed

0

None Installed

A

1x32 Standard

C

1x16 Standard

J

1x8 Standard

L

Dual 1x8 Standard

M

Dual 1x16 Standard

N

1x4 Standard

P

2x16 Standard

U

Dual 1x4 Standard

Splitter Qty Installed

0

None

1

One (1) Installed

2

Two (2) Installed

Key Locks

0	None (Pad Lock Ready)
A	Front Lock 1, Rear Lock 1
B	Front Lock 1, Rear Lock 2
C	Front Lock 1, No Rear Lock
D	Rear Lock 2, No Front Lock

Feeder Fiber Count

0	No Stub
2	2 Fibers
4	4 Fibers
6	6 Fibers
8	8 Fibers

Feeder Cable Length

000	0 Feet
025	25 Feet
100	100 Feet
200	200 Feet
300	300 Feet
500	500 Feet

Cable Type (Feeder Cable)

Adapters	
0	Adapters Only (No Pigtail for Feeder)
Pigtails	
A	Splice-Ribbon Pigtail Assy
C	Splice-Pigtails (900 Micron)
Stubs	
S	Ribbon OSP Cable
R	Ribbon IFC Cable
T	Loose Tube OSP Cable
V	Loose Tube IFC Cable
M	900um OFNR Cable

Optical Specifications

Fiber ModeSinglemode

Environmental Specifications

Environmental SpaceOutdoor

Qualification StandardsNEMA, Type 4

Packaging and Weights

Packaging quantity1

Packaging TypeBox | Carton

Regulatory Compliance/Certifications

FSB-SGJ27200C00000

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

