

LSX-LK5243-A-SPL



LSX Fiber Termination/Splice Panel 8 Ru, 288 - LC/UPC, Singlemode Ribbon

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	LGX

General Specifications

Functionality	Patching Splicing
Application	Used in LSX-style frames only
Cable Stub Type	Pigtails, ribbon
Color	Putty white
Color, front	White
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Rack Type	EIA 23 in
Rack Units	8
Shelf Movement	Fixed
Splicing Type	Mechanical, mass fusion
Total Ports, quantity	288

Dimensions

Height	279.4 mm 11 in
Width	482.6 mm 19 in
Depth	381 mm 15 in

LSX-LK5243-A-SPL

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

