

LSX-TK0000



LSX Fiber Termination Chassis 6 RU, 144 - LC/UPC

Product Classification

| | |
|-----------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch chassis |
| Product Series | LSX |

General Specifications

| | |
|-----------------------|-------------------------------|
| Functionality | Patching |
| Application | Used in LSX-style frames only |
| Color | Putty white |
| Growth Configuration | Fully loaded |
| Interface, front | LC/UPC |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 6 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 144 |

Dimensions

| | |
|--------|------------------|
| Height | 228.6 mm 9 in |
| Width | 482.6 mm 19 in |
| Depth | 304.8 mm 12 in |

Material Specifications

| | |
|---------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|------------|------------|
| Fiber Mode | Singlemode |
|------------|------------|

LSX-TK0000

Packaging and Weights

| | |
|--------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

