# NGF-CB1CL284124



Next Generation Frame (NGF) Fiber Termination/Splice Block, preterminated, 96 SC/UPC, singlemode, left oriented, putty white

#### **OBSOLETE**

This product was discontinued on: November 13, 2019

#### **Product Classification**

Regional Availability EMEA | Latin America | North America

**Product Type** Fiber patch/splice block

Product Series NGF

### General Specifications

Functionality Patching | Splicing

**Application** Used in NGF-style frames only

**Body Style** Left orientation

Cable Exit Location Rear, bottom side

**Color** Putty white

**Color, front** Putty white

Door Type, front Compression latch | Hinged

**Growth Configuration** Fully loaded

Interface, front SC/UPC

Rack Type NGF

**Shelf Movement** Fixed

**Total Ports, quantity** 96

#### Dimensions

**Height** 558.8 mm | 22 in


 Width
 166.878 mm | 6.57 in

 Depth
 495.3 mm | 19.5 in

**COMMSCOPE®** 

# NGF-CB1CL284124

# Ordering Tree



### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

## **Environmental Specifications**

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$ 

**Relative Humidity** Up to 80%, non-condensing

**Qualification Standards** Telcordia GR-449-CORE

## Packaging and Weights

**Included** Mounting hardware

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

# NGF-CB1CL284124

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

