RCP-172PUK06167



RapidFiber® Termination Panel, 24-Position 1RU, singlemode, SC/UPC to LC/UPC, 61 m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

General Specifications

Functionality Patching

Body Style Symmetrical

Cable Exit LocationRear, left side

 Cable Stub Type
 Indoor, microcable

Color Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontSC/UPCInterface, rearLC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Total Fibers, quantity 24

Total Ports, quantity 24

Transmission Standards IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in




RCP-172PUK06167

Depth 381 mm | 15 in

Cable Length 61 m | 200.131 ft

Ordering Tree



ONLY FOR MULTIMODE VERSION.1
ONLY AVAILABLE IN RISERPLENUM (P) CABLE TYPE?
RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.1
ONLY AVAILABLE IN 1C288 48U⁴

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A2/B2

COMMSCOPE®

RCP-172PUK06167

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+55 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +131 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Relative Humidity 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

