RDT-SJ24J2PC1002A



RapidFiber® FDT Distribution Terminal, 24-fiber, SC/APC, MPO at far end, 100 ft

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Fiber distribution terminal

Product Brand RapidFiber®

Product Series FDT

General Specifications

Adapters, quantity 24

Cable Color Yellow

Cable Entry Location Bottom left | Top left | Top right

Cable Type Indoor/outdoor - Stranded

Color Putty white

Front Cover Type Hinged with lock

Growth Configuration Fully loaded

Interface SC/APC

Interface, stub MPO

Mounting Wall

Port, quantity 24

Dimensions

 Height
 152.4 mm | 6 in

 Width
 228.6 mm | 9 in

 Depth
 101.6 mm | 4 in

 Cable Length
 30.48 m | 100 ft



RDT-SJ24J2PC1002A

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12

Packaging and Weights

Included Grommets

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant

