# RDT-XM04J00D1684A



RapidFiber® Mini-RDT, 1x4 Indexing Terminal, 3.6mm Black Riser I/O cable, female MPO at far end, 550 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Fiber distribution terminal, indexed

Product Brand RapidFiber®
Product Series Mini-RDT

### General Specifications

Adapters, quantity 4

Cable Color Black

Cable Entry Location Bottom left | Bottom right

Cable Type Indoor/outdoor - Stranded

**Color** Gray

**Distribution Type** 1 x 4 splitter

Fibers per Feeder Cable, quantity 12

Front Cover Type Hinged at top

Interface SC/APC

Interface, stub MPO
Mounting Wall

Port, quantity 4

Splitter, quantity

#### **Dimensions**

 Height
 203.2 mm | 8 in

 Width
 139.7 mm | 5.5 in

 Depth
 60.96 mm | 2.4 in

Page 1 of 2




# RDT-XM04J00D1684A

**Cable Length** 167.64 m | 550 ft

**Outer Cable Diameter** 4 mm | 0.157 in

## Dimension Drawing





Material Type Plastic

**Optical Specifications** 

Fiber Mode Singlemode

### **Environmental Specifications**

Environmental Space Indoor

Qualification Standards Telcordia GR-1435-CORE | Telcordia GR-3123-CORE | Telcordia GR-326-CORE

60 mm

(2.36 IN.)

Packaging and Weights

Packaging quantity

