# RDT-XM04J00P0924A



RapidFiber® Mini-RDT, 1x4 Indexing Terminal, 3mm Ivory Plenum cable, female MPO at far end, 300 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

#### **Product Classification**

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Fiber distribution terminal, indexed

**Product Brand** RapidFiber® **Product Series** Mini-RDT

### General Specifications

Adapters, quantity 4

**Cable Color** Ivory

**Cable Entry Location** Bottom left | Bottom right

Cable Type Plenum - Stranded

Color Gray

**Distribution Type** 1 x 4 splitter

Fibers per Feeder Cable, quantity 12

**Front Cover Type** Hinged at top

SC/APC Interface

MPO Interface, stub Wall

Splitter, quantity

#### Dimensions

Mounting

Port, quantity

Height 203.2 mm | 8 in Width 139.7 mm | 5.5 in Depth 60.96 mm | 2.4 in

**COMMSCOPE®** 


4


# RDT-XM04J00P0924A

 Cable Length
 91.44 m | 300 ft

**Outer Cable Diameter** 3 mm | 0.118 in

# Dimension Drawing





## Material Specifications

Material Type Plastic

**Optical Specifications** 

Fiber Mode Singlemode

## **Environmental Specifications**

Environmental Space Indoor

Qualification Standards Telcordia GR-1435-CORE | Telcordia GR-3123-CORE | Telcordia GR-326-CORE

Packaging and Weights

Packaging quantity

