

2-1671000-4



Fiber Optic Panel, 1U, 19 in, partially loaded with 12 blue LC/UPC Singlemode duplex adapters, black

Product Classification

| | |
|------------------------------|-------------------|
| Regional Availability | EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |

General Specifications

| | |
|------------------------------|------------------|
| Body Style | Symmetrical |
| Color | Black |
| Growth Configuration | Partially loaded |
| Interface, front | LC/UPC |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Total Ports, quantity | 24 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |

Material Specifications

| | |
|----------------------|---------------------------|
| Finish | Powder coated |
| Material Type | Hot deep galvanized steel |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant |

