# 131340-000 | FIST-GPS2-M-AAA-6

## FIST-GPS2 Fiber Termination/Splice Panel, 3RU, with 6 trays, ETSI width, gray

#### **Product Classification**

Regional Availability EMEA

Portfolio CommScope®

**Product Type** Fiber patch/splice panel

Product Brand FIST®

**Product Series** FIST-GPS2

## General Specifications

Functionality Patching | Splicing

**Application** Used in FIST-GR3-style frames only

Color Gray
Color, front Gray

Interface, front Unloaded

Rack Type ETSI 600 mm

Rack Units 3

**Shelf Movement** Sliding

#### **Dimensions**

 Height
 133.35 mm | 5.25 in

 Width
 531 mm | 20.906 in

### Material Specifications

Finish Powder coated

Material Type Galvanized steel

## **Environmental Specifications**

**Operating Temperature** -5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

Packaging and Weights



# 131340-000 | FIST-GPS2-M-AAA-6

**Included** Mounting hardware

Packaging quantity

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

