

# 1-1671437-1

Fiber Optic Termination Panel, 1U, 19 in, modular, flat, unloaded, black



## OBSOLETE

### Replaced By:

760242453  
AGL-1U-SL

AGILE 1U sliding panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel

## General Specifications

<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

