



12 Modular Jacks on a 100-Pair Wiring Block, With Mounting Legs

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Block

General Specifications

Product Design	110
ANSI/TIA Category	5
Wiring	T568B

Dimensions

Height	91.19 mm 3.59 in
Width	272.29 mm 10.72 in
Depth	82.55 mm 3.25 in
Compatible Conductor Gauge, solid	24 AWG 26 AWG

Material Specifications

Material Type	Copper alloy
----------------------	--------------

Mechanical Specifications

Plug Insertion Life, minimum	200 times
-------------------------------------	-----------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

