

1674981 | FD3-AC144J00JABP2-P



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 144F, SC/APC, no splitters, die. loose tube, 100 ft, 24F

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole
Splitter Slots, quantity	9

Dimensions

Height	762 mm 30 in
Width	533 mm 20.984 in
Cable Length	30.48 m 100 ft
Depth	356 mm 14.016 in
Enclosure Size	Extra small

Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

