

4-1671000-4

Fiber Optic Panel, 1U, 19 in, fully loaded with 24 blue LC/UPC SM duplex adapters, black



Product Classification

| | |
|------------------------------|-------------------|
| Regional Availability | EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |

General Specifications

| | |
|---------------------------------|--------------|
| Body Style | Symmetrical |
| Color | Black |
| Color, front | Black |
| Growth Configuration | Fully loaded |
| Interface, front | LC |
| Interface Feature, front | Standard |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Aluminum |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Above maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

