

# 760033928 | 600G2-1U-UP-FX

---



G2 1U Fixed Faceplate style, unloaded Fiber Optic Panel, without front faceplate, black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China   India
<b>Regional Availability Note</b>	Discontinued in all other regions since December 14, 2019 and replaced by 760234738   SD-1U-FX-UP in North America, Latin America and EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel

## General Specifications

<b>Application</b>	Accepts one G2 front faceplate   Accepts two RoloSplices with three trays each
<b>Color</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Patch Cord Routing</b>	Left sided   Right sided
<b>Rack Type</b>	EIA 19 in   ETSI 600 mm
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	355.6 mm   14 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Packaging and Weights

# 760033928 | 600G2-1U-UP-FX

---

**Included** Cable management kit | Cover | Instruction sheet | Label | Mounting hardware | Strain relief

**Weight, net** 3.266 kg | 7.2 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

