

CS6977-000 | BUDI-M-SEAL-6x10



BUDI™ Fiber Optic Cable Sealing Kit for up to 6 cables with 10mm cable diameter

Product Classification

| | |
|------------------------------|--------|
| Regional Availability | EMEA |
| Product Type | Seal |
| Product Brand | BUDI™ |
| Product Series | BUDI-M |

General Specifications

Application For holding up to 6 cables with 10mm cable diameter

Port Configuration

| | BUDI-S-SEAL-4x10 | BUDI-M-SEAL-6x10 | BUDI-S-SEAL-4x15 | BUDI-M-SEAL-6x15 | BUDI-S-SEAL-2x20 | BUDI-M-SEAL-3x20 | BUDI-S-SEAL-2x5 | BUDI-M-SEAL-2x5 | BUDI-S-SEAL-2x7 | BUDI-M-SEAL-2x7 | BUDI-S-PTS | BUDI-M-PTS | BUDI-S-SEAL-4x15-MINI-BO1 | BUDI-M-SEAL-4x15-MINI-BO1 |
|---------------------------|------------------|------------------|------------------|------------------|------------------|------------------|-----------------|-----------------|-----------------|-----------------|------------|------------|---------------------------|---------------------------|
| Max. cable diameter in mm | 10 | 10 | 15 | 15 | 20 | 20 | 5 | 5 | 7 | 7 | 5 | 5 | 8.2 | 8.2 |
| Wrap-around | Y | Y | Y | Y | Y | Y | N | N | N | N | Y | Y | Y | Y |
| Loop bracket | N | N | N | N | Y | Y | N | N | N | N | N | N | N | N |
| IP55 (vertical mounting) | Y | Y | Y | Y | Y | Y | Y | Y | Y | Y | N | N | Y | Y |
| Type of BUDI | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ | ■ ■ ■ |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |

CS6977-000 | BUDI-M-SEAL-6x10

UK-ROHS

Compliant

