

CY8504-000 | BUDI-S/M-INLINE-SEAL

BUDI™ Fiber Optic Cable Sealing Kit for cable feed-through from top for cables with up to 18mm cable diameter























Product Classification

Regional Availability	EMEA
Product Type	Seal
Product Brand	BUDI™
Product Series	BUDI-S

General Specifications

Application	For holding up to 2 cables with 18mm cable diameter
--------------------	---

Port Configuration

	BUDI-S-SEAL-4x10	BUDI-M-SEAL-6x10	BUDI-S-SEAL-4x15	BUDI-M-SEAL-6x15	BUDI-S-SEAL-2x20	BUDI-M-SEAL-3x20	BUDI-S-SEAL-24x5	BUDI-M-SEAL-24x5	BUDI-S-SEAL-24x7	BUDI-M-SEAL-24x7	BUDI-S-PTS	BUDI-M-PTS	BUDI-S-SEAL-4x15-MINI-BOT	BUDI-M-SEAL-4x15-MINI-BOT
Max. cable diameter in mm	10	10	15	15	20	20	5	5	7	7	5	5	8.2	8.2
Wrap-around	Y	Y	Y	Y	Y	Y	N	N	N	N	Y	Y	Y	Y
Loop bracket	N	N	N	N	Y	Y	N	N	N	N	N	N	N	N
IP55 (vertical mounting)	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	N	N	Y	Y
Type of BUDI	  		 		 		 		 		 		 	

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

