

# F3X-E288JJBBB0000

---

FDH 3000 Small Fiber Distribution Cross-Connect/Distribution Hub, 144F, SC APC, dielectric loose tube, 100 ft

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber cross-connect hub
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Dielectric - Loose Tube
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	2
<b>Distribution Ports, quantity</b>	288
<b>Fibers per Distribution Cable, quantity</b>	144
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pad
<b>Splitter Slots, quantity</b>	12

## Dimensions

<b>Height</b>	762 mm   30 in
<b>Width</b>	685.8 mm   27 in
<b>Depth</b>	457.2 mm   18 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Small

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Environmental Specifications

<b>Environmental Space</b>	Above ground
----------------------------	--------------

# F3X-E288JJBBB0000

---

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

