

F3X-J576NJB BBBB00



FDH 3000 Fiber Distribution Cross-Connect Hub, 144F dist., SC UPC, die. Loose tube, 100 ft

Product Classification

Regional Availability	North America
Product Type	Fiber cross-connect hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	864
Fibers per Distribution Cable, quantity	288
Interface, Input	SC
Interface Feature, Input	Standard
Mounting	Pad

Dimensions

Height	1,244.6 mm 49 in
Width	1,193.8 mm 47 in
Depth	508 mm 20 in
Cable Length	30.48 m 100 ft
Enclosure Size	Large

Material Specifications

Finish	Powder coated
---------------	---------------

F3X-J576NJB BBBB00

Material Type Steel

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet