FD3-MM288J00M0ME0C



Indoor FDH 3000 w/ 288f Shell, 288f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Spliced Stranded Loose Tube Pigtails

Indoor FDH 3000 w/ 288f Shell, 288f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Spliced Stranded Loose Tube Pigtails

Product Classification

Cable Length

Regional Availability	North America	
Product Type	Fiber distribution hub	
Product Series	IFDH 3000	
General Specifications		
Functionality	Patching Splicing	
Access	Front	
Adapters, quantity	288	
Cable Type	Pigtails - Stranded	
Color	Putty white	
Distribution Cables, quantity	24	
Fibers per Distribution Cable, quantity12		
Fibers per Feeder Cable, quantity	48	
Front Door Type	Single hinged	
Interface	SC/APC	
Mounting	Wall	
Port, quantity	288	
Splitter Slots, quantity	18	
Dimensions		
Height	736.6 mm 29 in	
Width	533.4 mm 21 in	
Depth	368.3 mm 14.5 in	

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2024

30.48 m | 100 ft



FD3-MM288J00M0ME0C

Enclosure Size		Medium
Material Specifications		
Finish		Powder coated
Material Type		Aluminum
Optical Specifications		
Fiber Mode		Singlemode
Environmental Specifications		
Environmental Space		Indoor
Packaging and Weights		
Packaging quantity		1
Regulatory Compliance/Certifications		
Agency	Classification	
CHINA-ROHS	Above maximum concentration value	
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance	
ROHS	Compliant/Exempted	
UK-ROHS	Compliant/Exempted	



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2024

