


FD3-MM288J00V00E0A



IFDH 3000 Indoor Fiber Distribution Hub, 288F, SC/APC, loose tube /stranded pigtails, spliced input, 12F feeder

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Functionality	Patching Splicing
Access	Front
Adapters, quantity	288
Cable Type	Pigtails - Stranded
Color	Putty white
Distribution Cables, quantity	24
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	12
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	288
Splitter Slots, quantity	18

Dimensions

Height	736.6 mm 29 in
Width	533.4 mm 21 in
Depth	368.3 mm 14.5 in
Cable Length	30.48 m 100 ft
Enclosure Size	Medium

FD3-MM288J00V00E0A

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Optical Specifications

Fiber Mode	Singlemode
------------	------------

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

