FD3-MN432J00LABCAB



IFDH 3000 Indoor Fiber Distribution Hub, 432F, SC/APC, riser I/O LT 50' stub, 24F 100' stub feeder cable

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series IFDH 3000

General Specifications

Functionality Patching | Splicing

Access Front
Adapters, quantity 432

Cable Type Indoor/outdoor - Stranded

Color Putty white

Distribution Cables, quantity 3

Fibers per Distribution Cable, quantity 144
Fibers per Feeder Cable, quantity 24

Front Door Type Single hinged

Interface SC/APC

MountingWallPort, quantity432Splitter Slots, quantity18

Dimensions

Height 990.6 mm | 39 in

Width 358.1 mm | 14.098 in

 Depth
 368.3 mm | 14.5 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Large

COMMSC PE°

FD3-MN432J00LABCAB

Material Specifications

Finish Powder coated

Material Type Aluminum

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

