FDT-CJ048NXR5000



iFDT Indoor Fiber Distribution Terminal, 48-fiber, SC/APC, ribbon IFC cable, 5000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability North America

Product Type Fiber distribution terminal

Product Series IFDT

General Specifications

Adapters, quantity 48

 Cable Entry Location
 Bottom right | Top right

Cable TypeIFC - RibbonColorPutty whiteFront Door TypeDouble hingedGrowth ConfigurationFully loaded

Interface SC/APC

Interface, stubNo connectorLock TypePadlock ready

Mounting Wall
Port, quantity 48

Dimensions

 Height
 476.25 mm | 18.75 in

 Width
 368.3 mm | 14.5 in


 Depth
 127 mm | 5 in

 Cable Length
 1524 m | 5000 ft

Ordering Tree



FDT-CJ048NXR5000



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1



FDT-CJ048NXR5000

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

