# FDT-EJ096NXV3000



# iFDT Indoor Fiber Distribution Terminal, 96-fiber, SC/APC, loose tube IFC cable, 3000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

#### Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

#### General Specifications

Adapters, quantity	96
Cable Entry Location	Bottom right   Top right
Cable Type	IFC - Stranded
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	SC/APC
Interface, stub	No connector
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	96
Dimensions	
Height	825.5 mm   32.5 in
Width	373.38 mm   14.7 in
Depth	127 mm   5 in
Cable Length	914.4 m   3000 ft


### Ordering Tree

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023



## FDT-EJ096NXV3000



#### Material Specifications

 Finish
 Powder coated

 Material Type
 Steel

#### **Optical Specifications**

Fiber Mode

Singlemode

#### Environmental Specifications

Environmental Space Qualification Standards

Indoor

1

NEMA, Type 12 | Telcordia GR-2898-CORE

#### Packaging and Weights

Packaging quantity

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023



## FDT-EJ096NXV3000

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023

