## FL1-G377NNN1-1100N



FL1000 Fiber Wall Box, 2-door, singlemode SC/UPC, 12-ports, with pigtails and splice tray, 1 cable clamp, 1 compression fitting

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

#### **Product Classification**

 Regional Availability
 North America

 Product Type
 Fiber wall box

 Product Series
 FI 1000

#### General Specifications

FunctionalityPatching| SplicingApplicationPatching| Splicing

Adapter Packs Included, quantity 2

Adapters, quantity 12

Cable Clamps, quantity 1

Cable Compression Fittings, quantity 1

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable TypePigtails - Stranded

**Color** Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface SC/UPC
Mounting Wall

**Splicing Type** Bare fusion

Total Fibers, quantity 12

Total Ports, quantity 12

**Dimensions** 

COMMSCOPE®


# FL1-G377NNN1-1100N


 Height
 433 mm | 17.047 in

 Width
 511 mm | 20.118 in

 Depth
 156.97 mm | 6.18 in

### Outline Drawing





### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

**Environmental Specifications** 

Environmental Space Indoor

**Qualification Standards** NEMA type 12

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

**COMMSCOPE®** 

# FL1-G377NNN1-1100N

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

