FL1-G677NNN2-2222D



FL1000 Fiber Wall Box, 2-door, singlemode SC/UPC, 12-ports, with softwall-bundled pigtails and splice tray, 2 cable clamps, 2 compression fittings, 2 grounding kits, 2 strength member tie-offs, 2 key locks

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional Availability	North America	
Product Type	Fiber wall box	
Product Series	FL1000	
General Specifications		
Application	Patching Splicing	
Adapter Packs Included, quantity	2	
Adapters, quantity	12	
Cable Clamps, quantity	2	
Cable Compression Fittings, quantity	2	
Cable Entry Location	Bottom left Bottom right Top left Top right	
Cable Type	Pigtails - Stranded	
Color	Putty white	
Door, quantity	2	
Front Door Type	Single hinged	
Growth Configuration	Fully loaded	
Interface	SC/UPC	
Lock Type	Key lock	
Mounting	Wall	
Splicing Type	Heat shrink, mass fusion	
Total Fibers, quantity	12	
Total Ports, quantity	12	

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023




FL1-G677NNN2-2222D


Dimensions

Height	433 mm 17.047 in
Width	511 mm 20.118 in
Depth	156.97 mm 6.18 in

Outline Drawing



. .



Material Specifications	
Finish	Powder coated
Material Type	Steel
Optical Specifications	
Fiber Mode	Singlemode
Environmental Specifications	
Environmental Space	Indoor
Qualification Standards	NEMA type 12
Dadyacian and Mainhte	

Packaging and Weights

Included

Packaging quantity

Two grounding kits | Two tie-off adapters

1

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023



FL1-G677NNN2-2222D

Packaging Type

Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximu
REACH-SVHC	Compliant as p

ROHS



UK-ROHS

maximum concentration value ant as per SVHC revision on www.commscope.com/ProductCompliance Compliant/Exempted Compliant/Exempted

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023

