FL1-H3777NN1-1100A



FL1000 Fiber Wall Box, 2-door, singlemode SC/UPC, 24-ports, with pigtails and splice tray, 1 cable clamp, 1 compression fitting, 1 key lock

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- · Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

 Regional Availability
 North America

 Product Type
 Fiber wall box

 Product Series
 FI 1000

General Specifications

FunctionalityPatching| SplicingApplicationPatching| Splicing

Adapter Packs Included, quantity 4

Adapters, quantity 24

Cable Clamps, quantity 1

Cable Compression Fittings, quantity 1

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable TypePigtails - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface SC/UPC

Lock Type Key lock, type A

Mounting Wall

Splicing Type Bare fusion

Total Fibers, quantity 24
Total Ports, quantity 24

COMMSC PE®

FL1-H3777NN1-1100A


Dimensions

 Height
 590 mm | 23.228 in

 Width
 551 mm | 21.693 in

 Depth
 156.97 mm | 6.18 in

Outline Drawing



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Packaging quantity 1

Page 2 of 3

FL1-H3777NN1-1100A

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

